4343W

Digital Radiography





OVERVIEW

Varex 4343W is a lightweight wireless flat panel detector designed for digital radiographic systems. It fits standard 17" x 17" bucky trays and its 5 GHz wireless connection provides robust communication in table, above table, chest stand, and mobile cart applications. Option for in-bucky inductive charging eliminates the need to change batteries. In case inductive charging is not utilized, the detector supports battery hot swap as well.

Varex 4343W comes in a plastic housing and it is the first panel on the market with an Ingress Protection rating of IP68. This industry-leading housing design is extremely robust and supports uniform loads up to 300 kg and concentrated loads up to 200 kg.

FEATURES AND BENEFITS

- Improved ergonomics including hand grips
- Reduced weight (3.1 kg / 3.3 kg)
- Ingress Protection rating IP68
- Improved wireless performance (5 GHz)
- Reduced cycle time < 5 s
- Battery hot swap (3 mins. up-time)
- Inductive Charging inside bucky
- Enhanced Automatic Exposure Detection (AED)
- Gyroscope (X,Y,Z)
- Hall sensor for bucky positioning
- Shock and free fall sensors
- Dynamic integration time (350-4000 ms)
- Dual Energy capable
- Supports panel sharing
- Customizable overlay

APPLICATIONS1

Digital radiography

TECHNICAL SPECIFICATIONS

SENSOR

| Scintillator DRZ+ / Standard Csl / Premium Csl |
|--|
| Pixel Matrix |
| Pixel Pitch |
| Active Area (DRZ+) |
| (CsI) |

IMAGE QUALITY (typical)

| | DRZ+ | Standard Csl | Premium Csl |
|---------------|------|--------------|-------------|
| DQE @ 0 lp/mm | 39% | 65% | 76% |
| DQE @ 1 lp/mm | 28% | 54% | 62% |
| DQE @ 3 lp/mm | 9% | 29% | 32% |
| MTF @ 1 lp/mm | 56% | 61% | 57% |
| MTF @ 2 lp/mm | 24% | 32% | 28% |
| MTF @ 3 lp/mm | 10% | 17% | 14% |

COMMUNICATIONS

| Wireless Interface | 802.11 n/ac (5 GHz) |
|----------------------------|--------------------------------------|
| Wireless Modes | . Station (STA) or Access Point (AP) |
| Cycle Time @ 550 ms | <5 sec |
| X-Ray Window | 350-4000 ms |
| Exposure Control - Inputs | Prepare, Exposure-Request |
| Exposure Control - Outputs | Expose-OK |
| | |

ADVANCED FEATURES

| Inductive Charging | 15 Watt In-bucky Charger |
|-----------------------|--|
| Battery Hot Swap | Maintains power/connection for 3 minutes |
| Gyroscope | Orientation (x, y, z) Status |
| Bucky Retrofit Option | Inductive Charger |

MECHANICAL

| Uniform Load Across Entire Surface | 300 kg |
|--|-----------|
| Concentrated 40 mm Diameter Load at the Center | 200 kg |
| Dimensions | x 15 mm |
| Weight (DRZ+ / CsI) | /3.3 kg |
| Housing Material | . Plastic |

ENVIRONMENTAL

| Ingress Protection IP6 | 8 |
|-----------------------------------|---|
| Operating Temperature 10°C to 40° | С |
| Storage Temperature20°C to +55° | C |
| Humidity (non-condensing) | % |


BATTERY


| Type | Lithium Polymer (prevents overcharging) |
|-------------------|---|
| Charge Capability | 1600 images over 8 hrs. |
| Expected Life | 500 cycles of charge/discharge |

REGULATORY

| U.S | ANSI/AAMI ES 60601-1:2012 |
|--------|--------------------------------|
| Canada | . CAN/CSA C22.2 No. 60601-1:14 |
| EU | IEC/EN 60601-1:2012 |

¹ Unless otherwise specified, Varex Imaging Flat Panel X-ray Detectors are components intended to be integrated into products by X-ray system manufacturers. System manufacturers are responsible for qualifying and validating their products for their intended uses and meeting all applicable regulatory requirements.





Receiver for Inductiv Charger

Varex Imaging Corporation

USA HEADQUARTERS
Salt Lake City, UT
P: +1-801-972-5000
Walluf
P: +49-6123-971-300
Wuxi
P: +49-6123-971-300
P: +86 510 8592-9201

CHINA
Wuxi
For a complete listing of our global offices, visit www.vareximaging.com

©2020 Varex Imaging Corporation. All Rights reserved. Production of any of the material contained herein in any format or media without the express written permission of Varex Imaging Corporation is prohibited.