## **Product Specifications -**

	ECG ACQUISITION		ERMAL RECORDING	
ECG Acquisition	12 bits; 1000 samples/ sec/ channel	Recording System	Thermal printer, 8 dots/ mm, 72 mm usable print width	
ADC Resolution	2.55 μV/LSB	D T (C )	·	
Input Dynamics	DC offset: ± 300mV; AC Differential: ± 5mV in the pass band	Paper Transport Speed	5 mm/sec or 12.5 mm/sec or 25mm/ sec or 50 mm/sec	
ECG Lead	Standard 12 leads or Cabrera; Acquired 8 leads & Reconstructed 4 leads (Lead III, Lead aVR, Lead aVL, Lead aVF)	Thermal Paper	In rolls: Height 80mm, Length 20m, gridded	
	Manual: 2.5 - 5 -10 - 20 mm/mV ± 5%	Print Channel	3 Channel + 1 Rhythm or 3 Channel;	
Recording Sensitivity	Auto: Dependent on the signal		Manual: 3 Ch.	
,	strength, Optimizes automatically to 2.5-5-10-20 mm/mV ± 5%	Print Formats	Auto: 3 Ch, 3 Ch + 1 Rhythm with selectable print durations of 2.5 secs./	
Input Impedance	> 10 MΩ @ 10 Hz		5 secs./ 10 secs.	
Frequency Response	0.05 Hz to 150 Hz (-3dB) without Mains /Muscle and ADF Filters		PC CONNECTIVITY	
Time Constant	> 3.2 seconds	Paperless Workflow	ECG Data Export feature to multiple formats enables this specification	
CMRR	> 90dB @ 50Hz	PC Connectivity	Real-time ECG transfer to PC over USB	
DF Protection	Internal	. a commeditivity	(Optional)	
ECG PROCESSING		BATTERY & POWER		
ECG Analysis & Interpretation	Gender, Age & Race specific Advanced ECG Analysis & Interpretation - Glasgow ECG Interpretation Algorithm in Auto mode	Battery	Rechargeable Lithium battery 11.1Vdc, 3000mAh	
		Mains Protection	Fuse: T2A 250 V	
ECG Analysis Sampling Rate	500 samples/ second (sps)	Battery Protection	In built PCM Module	
Filters	Mains interference/ Muscle filter: Linear phase digital 50 Hz Notch filter with selectable 32 Hz.	Power Supply	100-240 VAC; 50/60 Hz	
		Battery Charging Time	Approximately 3 hours 30 minutes from total discharge (Unit off)	
	Anti-drift filter: Selectable Digital 0.5Hz Anti Drift High pass linear phase filter	Power Consumption	Less than 60VA	
Pacemaker	Recognizes pulse in accordance with	ENVIRONMENT SPECIFICATIONS		
Recognition	applicable IEC standards	Operating Temperature	+10 to +40 °C	
Signal Memory	10 Seconds for each lead in Auto mode	Relative Humidity	Upto 95% RH Non-condensing	
Operating Modes	Manual: acquisition and printing in real time	Storage/ Transport Temperature	-10 °C to 50 °C	
	<b>Auto:</b> simultaneous acquisition and printing	Relative Humidity	Upto 95% RH Non-condensing	
Heart Rate Meter	30 to 240 BPM ±10% or ±5 BPM,	,		
whichever is greater		PHYSICAL SPECIFICATIONS		
	ISPLAY & STORAGE	Dimension	Approx. 300mm x 260mm x 80 mm (length x width x height)	
Display	4.3 inch Color TFT LCD with 480 x 272 pixel resolution; 65k Color	Weight	Approx. 2 Kgs.	
Keyboard	Silicone Rubber keypad with 23 keys & 4 LED indicators		STANDARD ACCESSORIES	
Indicators	Mains Connection, Battery Charging,	Patient Cable	1 No.	
A 171 L D	Battery Low & System Errors	Limb Electrodes	4 Nos.	
Audible Beep	Heart Rate and Key Press	Chest Electrodes	6 Nos.	
Startup Time	< 4 seconds	Thermal Paper Roll	1 No.	
Record Storage	250 ECGs in internal memory with cyclic overwrite	Cardijelly Bottle	1 No.	
,		User Manual	1 No.	
SAFETY CLASSIFICATION		Earth cable	1 No.	
Safety Classification	Class I with internal power supply	Power Cord	1 No.	
Degree of Protection	Type CF		*Technical specification subject to change	

ISO 13485:2016 CERTIFIED COMPANY ISO 9001:2015 CERTIFIED COMPANY

BPL Medical Technologies Private Limited Regd. Office: 11th KM, Bannerghatta Road, Arakere, Bangalore - 560076, India. Toll Free: 1800-4252355

Website: www.bplmedicaltechnologies.com For Enquiries: sales.medical@bpl.in CIN: U33110KA2012PTC067282







Happier Living Everyday